## **engineering** innovations worldwide



## talos

state-of-the-art device handling system





## talos device handling system

made for all testers



· most flexible and easy-to-use tri-temp pick & place device handling system

 $\cdot$  device range from 1.0 x1.0 x 0.4 mm (0.04" x 0.04" x 0.02") to 70.0 x 70.0 x 10.0 mm (2.76" x 2.76" x 0.4")

 $\cdot$  tray, tube, and tape loading  $\mid$  unloading possible



sealed doors to

avoid icing at cold test
operation processes

FIFO or BIN sort mode with free tray | tube | tape assignment

4+1 axis pick-and-place system (x | y | z1 | theta | z2) with high contact force of 450N (optional up to 800 N)

15.6" widescreen HMI with multi-touch capability

laser distance sensor
+ camera for x|y|z
teaching

6

active thermal control system (ATC)

# enhancing semiconductor industry efficiency with innovative test equipment solutions

#### Adaptive for most existing setups:

existing sockets, boards, etc. can be used without any modifications  $% \left( x\right) =\left( x\right) +\left( x\right$ 

#### **Docking interface:**

standard docking interface compatible with all testers

#### Cable dock engineering board support:

engineering boards with cable docks can be used with a special board support

#### Remote control:

remote control via Ethernet

#### Lowest time to test:

switching from one package to the next in under 5 minutes

#### Test parameters stored in recipe files:

no mechanical fine alignment is necessary

#### Automated testing:

multiple test cycles at different temperatures without requiring user interaction

#### **Testing temperature range:**

from -60 °C to +175 °C (-76 °F to +347 °F) with an active thermal control system (ATC) for cold/hot tests, allowing for tri-temp testing

#### Portability:

optimized for smooth and independent handling by one person

#### **Compact footprint:**

with the esmo phoenix cart the smallest test cell footprint in the market

#### Basic configuration or a customized modular handling system:

tailored to individual requirements and intended use

#### Reliability and maintenance:

high mean time between failures (MTBF) values, low maintenance efforts





## handling key features

exceptional accuracy and reliability with advanced 4+1-axis portal pick-and-place robot system

versatile loading and unloading options, incl. manual tray, tube or tape loading

free PIN1 orientation for seamless integration

high contact force of 350 N (700 N contact force optionally available)

user-friendly 15.6" widescreen HMI featuring multi-touch capability

integrated camera system for precise pick-and-place position teaching

FIFO or bin sort mode, offering free tray | tube assignment

RS232 or optional GPIB tester interfaces for seamless connectivity

capacity: 8 low-/high-profile JEDEC trays | autom. tray stacker 15 trays

adapterplates for 2" and 4" waffle packs available

quick changeover to tube loading option within 5 minutes only

freely programmable BIN classification with input | output assignment

low jam rate: max. 1 error per 8 hours or less



capacity: max. of 8 input | 8 output tubes

max. tube dimensions: 21 mm x 12 mm x 530 mm (0.8" x 0.5" x 21")

max. device length: 17 mm

tube compatibility: supports plastic and/or metal tubes

low jam rate: max. 1 error per 8 hours or less

compatible with tray / tube unloading option

module exchange: toolless module exchange with quick-release lock

tape widths: modules available for 8 to 32 mm tape widths

cold and hot sealing possible

low Jam rate: max. 1 error per 8 hours or less

# temperature control featuresactive thermal control option (ATC)

closed loop temperature control with an integrated sensor in the temperature head

highest accuracy achieved by directly measuring the temperature at the heat sink, in conductive contact with the device

ability to control high IC power dissipation during electrical testing

software-operated air flow control system with human-machine interface (HMI) feedback included

set temperature can be changed from the tester via GPIB or RS232:

- ||| fine adjustment during testing
- ||| single-insertion at multiple test temperatures is possible
- ||| multiple tests at different temperatures without requiring user interaction

fully integrated cooling unit controlled by the handler software.


two configuration options available: electrical air chiller and LN2 heat exchanger.

- ||| electrical air chiller with a system specification of -50 °C (-58 °F) DUT typical junction temperature
- ||| LN2 heat exchanger with a system specification of -60 °C (-76 °F) DUT typical junction temperature

system interior is sealed and purged to prevent icing

modular and expandable temperature system





## various optional features

tray | tape | tube loading/unloading

vision alignment

temperature control + cooling options

high contact force (up to 700N)

traystacker

dual ionizer

air dryer unit

vacuum generator

multi-site-contacting

code reader

ESD acryl glass cover

external status lights

z2 with contact force control feature

junction control (JC) + power dissipation compensation (PDC)

vision system option for small-device contact position correction

self-teaching system, no adjustment required

no mechanical pre-alignment required

for device sizes of 1 x 1 mm to 5 x 5 mm

contact force of z-axis motor up to 700 N (instead of 350 N)

field upgradeable

compatible with standard conversion kit

higher contact force available on request

to protect sensitive parts from damage due to electro-static discharge self-regulating ionization level

2 electrical air fans (compressed air not required)

adjustable direction and blowing speed

decay time: at 1,000 V to 100 V in less than 3 s

### Here for you, wherever you are:

### Worldwide Sales + Service Network





esmo Europe Rosenheim

esmo AG Brueckenstrasse 1 83022 Rosenheim Germany

P +49 (8031) 233 88 0 F +49 (8031) 233 88 10 sales@esmo-ag.com esmo USA California

esmo USA Corp. 1020 Winding Creek Road Suite #120 Roseville | CA 95678 USA

P +1 (916) 307 6345 F +1 (916) 307 6341 sales@esmo-usa.com esmo Asia Singapore

esmo Asia Pte. Ltd. 15 Tai Seng Drive #01–02 Singapore 535220 Singapore

P +65 (656) 288 57 F +65 (656) 288 60 sales@esmo-asia.com esmo China Shanghai

esmo Asia North Co. Ltd. Building 5-6 N. 388 Xin Run Rd. Xin Qiao Industrial Zone Song Jiang District 201612 Shanghai · China

P +86 (21) 5768 7228 + ex. 201 F +86 (21) 5768 7132 info@esmo-ag.com.cn esmo Taiwan Zhubei

esmo TW Ltd. Co. 9F., No. 247, Dong Sec. 1, Guangming 6th Rd., Zhubei City · Hsinchu County 302044 · Taiwan (R.O.C.)

M +886 932-290-662 M +886-988-313-705 sales@esmo-asia.com